30 mm (1½") photomultiplier 9125B series data sheet

electron tubes

1 description

The 9125B is a 30 mm (11/8") diameter, end window photomultiplier with blue-green sensitive bialkali photocathode and 11 high gain, high stability, SbCs dynodes of linear focused design. The 9125WB and 9125QB are variants for applications requiring uv sensitivity.

2 applications

- wide range of applications
- spectroscopy
- x-ray & gamma-ray spectroscopy
- · photon counting of bio- and chemi-luminescent samples

3 features


- high gain
- low operating voltage
- good SER
- · good pulse height resolution

4 window characteristics

	9125B	9125WB	9125QB*
	borosilicate	UV glass	fused silica
spectral range**(nm) refractive index (n _d)	280 - 630	170 - 630	160 - 630
	1.49	1.48	1.46
K (ppm)	300	8500	<10
Th (ppb)	250	30	<10
U (ppb)	100	30	<10

^{*} note that the sidewall of the envelope contains graded seals of high K content
** wavelength range over which quantum efficiency exceeds 1 % of peak

⁵ typical spectral response curves




6 characteristics

	unit	min	typ	max
photocathode: bialkali active diameter quantum efficiency at peak luminous sensitivity with CB filter with CR filter	mm % µA/lm	7	25 28 65 11	
dynodes: 11LFSbCs anode sensitivity in divider A: nominal anode sensitivity max. rated anode sensitivity overall V for nominal A/Im overall V for max. rated A/Im gain at nominal A/Im	A/lm A/lm V V x 10 ⁶		200 2000 850 1100	1100
dark current at 20 °C: dc at nominal A/Im dc at max. rated A/Im	nA nA		0.2	5
dark count rate afterpulse rate: afterpulse time window pulsed linearity (-5% deviation)		0.1	100	6.4
divider A divider B pulse height resolution: single electron peak to valley	mA mA ratio		25 100 2	
¹³⁷ Cs with 1" x 1" Nal(T1) rate effect (I _a for Δg/g=1%): magnetic field sensitivity: the field for which the output decreases by 50 %	μΑ		7.5 20	
most sensitive direction temperature coefficient:	T x 10 ⁻⁴ % °C ⁻¹		2 ± 0.5	
timing: single electron rise time single electron (fwhm) single electron jitter (fwhm) transit time weight:	ns ns ns ns		4.5 7.5 4 33 50	
maximum ratings: anode current cathode current gain	μΑ nA x 10 ⁶			100 50 30
sensitivity temperature V (k-a) ⁽¹⁾ V (k-d1) V (d-d) ⁽²⁾	A/Im °C V V	-30		2000 60 2000 300 300
ambient pressure (absolute)	kPa			202

⁽¹⁾ subject to not exceeding max. rated sensitivity (2) subject to not exceeding max rated V(k-a)

7 typical voltage gain characteristics




voltage divider distribution

k	c d	l ₁ d	2 · · · · · · · ·	d ₈	dg	d ₁	_o d	11 4	1
Α	2R	R		R	R	R	R	R	Standard
В	2R	R		R	2R	3R	4R	3R	High Pulsed Linearity

Characteristics contained in this data sheet refer to divider A unless stated otherwise.

9 external dimensions mm



10 base configuration (viewed from below)





'ic' indicates an internal connection

Our range of B14B sockets, available for this series, includes versions with or without a mounting flange, and versions with contacts for mounting directly onto printed circuit boards.

11 ordering information

The 9125B meets the specification given in this data sheet. You may order variants by adding a suffix to the type number. You may also order options by adding a suffix to the type number. You may order product with specification options by discussing your requirements with us. If your selection option is for one-off order, then the product will be referred to as 9125A. For a repeat order, Electron Tubes will give the product a two digit suffix after the letter B, for example B21. This identifies your specific requirement.





12 voltage dividers

The standard voltage dividers available for these pmts are tabulated below:

	k	d ₁ d ₂	2 · · · · · · · · · · · · · · · · · · ·	d ₇	d ₈	d ₉	d ₁₀ d	₁₁ a	
C637A	2R	R		R	R	R	R	R	
C637C	2R	R		R	2R	3R	4R	3R	
C686	2 V	V		V	V	V	V	V	

 $R = 300 \text{ k}\Omega$

Electron Tubes Limited Bury Street, Ruislip Middx HA4 7TA, UK tel: +44 (0) 1895 630771 fax: +44 (0) 1895 635953 e-mail:

Electron Tubes Inc. 100 Forge Way, Unit F Rockaway, NJ 07866, USA tel: (973) 586 9594 toll Free: (800) 521 8382 fax: (973) 586 9771 info@electron-tubes.co.uk e-mail: sales@electrontubes.com The company reserves the right to modify these designs and specifications without notice. Developmental devices are intended for evaluation and no obligation is assumed for future manufacture. While every effort is made to ensure accuracy of published information the company cannot be held responsible for errors or consequences arising therefrom.



an ISO 9001 registered company

© Electron Tubes Limited, 2001 DS 9125B Series Issue 3 01 June 2001